



## ENVIRONMENTAL CHAMBER BCEV-102

## ENVIRONMENTAL CHAMBER BCEV-102

A perfect appliance for environmental simulation that consistently is designed to give you a lasting performance. It precisely performs controlled material tests, aging tests and function tests. Durable interiors along with safety features make it an ideal option.

Used in Widely used for controlled testing of substances of specified environmental conditions. A perfect partner for stability and stress testing, shelf life studies and other biological research..

Also known as Environment Simulation Chamber, Test Chamber, Laboratory Environmental Chamber.

## BCEV-102 ENVIRONMENTAL CHAMBER

Stainless steel SUS304 inner chamber and cold rolled steel plate with electrostatic powder spraying exterior

Forced cold-air circulation system with low-noise axial flow and centrifugal fan ensures the temperature uniformity

Warped type evaporator

Air cooling system

Digital Controller with fix running mode

Refrigerant: CFC free R404A

Door with non-condensation observation window and illumination

Silicon rubber material ensures tight sealing and prevents heat loss

Test hole with a diameter of 1 set x 50 mm

Heat insulation: PU FOAM + Glass fibre cotton material

Brazed plate heat exchangers (BHEs) offers highest heat transfer performance

High quality hermetic compressor: Low energy consumption, low noise level and low heat dissipation

Noise level:  $\leq 65$  dB

Castors: 4 units for easy handling

Safety features:

Over-temperature, Over-current, Electric leakage, Power phase, Fuse, Ground, and Water shortage Protection

Over-pressure, Over-heating, Over-current protection for compressor

## SPECIFICATIONS

Model	BCEV-102
Capacity	100 L
Temperature Range	0-65°C
Temperature Accuracy	$\pm 1^\circ\text{C}$
Temperature Uniformity	$\pm 2.0^\circ\text{C}$
Temperature Fluctuation	$\pm 0.5^\circ\text{C}$
Temperature Resolution	0.1°C
Temperature Sensor	Pt 100 $\Omega$
Humidity Range	55-95 %RH
Humidity Uniformity	$\pm 2.0$ %RH
Humidity Fluctuation	$\pm 2.0$ %RH
Humidity Sensor	Dry and wet bulb sensor
Heating Rate	2-3°C/min
Cooling Rate	1-2°C/min

Timer Range	1-9999 min
Shelves	2
Load per Shelf	15 kg
Inner Dimension	380x350x750 mm
Overall Dimension	650x475x1485 mm
Weight (Net/Gross)	99/105 kg
Power	500 W
Power Supply	120V/220V/240V/380V/415V, 50Hz/60Hz



**Biolab Scientific Ltd.**

3660 Midland Avenue, Suite 300, Toronto, Ontario M1V 0B8, Canada

Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)