



ENVIRONMENTAL CHAMBER BCEV-103

ENVIRONMENTAL CHAMBER BCEV-103

A perfect appliance for environmental simulation that consistently is designed to give you a lasting performance. It precisely performs controlled material tests, aging tests and function tests. Durable interiors along with safety features make it an ideal option.

Used in Widely used for controlled testing of substances of specified environmental conditions. A perfect partner for stability and stress testing, shelf life studies and other biological research..

Also known as Environment Simulation Chamber, Test Chamber, Laboratory Environmental Chamber.

BCEV-103 ENVIRONMENTAL CHAMBER

Stainless steel SUS304 inner chamber and cold rolled steel plate with electrostatic powder spraying exterior

Forced cold-air circulation system with low-noise axial flow and centrifugal fan ensures the temperature uniformity

Warped type evaporator

Air cooling system

Digital Controller with fix running mode

Refrigerant: CFC free R404A

Door with non-condensation observation window and illumination

Silicon rubber material ensures tight sealing and prevents heat loss

Test hole with a diameter of 1 set x 50 mm

Heat insulation: PU FOAM + Glass fibre cotton material

Brazed plate heat exchangers (BHEs) offers highest heat transfer performance

High quality hermetic compressor: Low energy consumption, low noise level and low heat dissipation

Noise level: ≤ 65 dB

Castors: 4 units for easy handling

Safety features:

Over-temperature, Over-current, Electric leakage, Power phase, Fuse, Ground, and Water shortage Protection

Over-pressure, Over-heating, Over-current protection for compressor

SPECIFICATIONS

Model	BCEV-103
Capacity	150 L
Temperature Range	0-65°C
Temperature Accuracy	$\pm 1^\circ\text{C}$
Temperature Uniformity	$\pm 2.0^\circ\text{C}$
Temperature Fluctuation	$\pm 0.5^\circ\text{C}$
Temperature Resolution	0.1°C
Temperature Sensor	Pt 100 Ω
Humidity Range	55-95 %RH
Humidity Uniformity	± 2.0 %RH
Humidity Fluctuation	± 2.0 %RH
Humidity Sensor	Dry and wet bulb sensor
Heating Rate	2-3°C/min
Cooling Rate	1-2°C/min

Timer Range	1-9999 min
Shelves	3
Load per Shelf	15 kg
Inner Dimension	500x370x800 mm
Overall Dimension	770x495x1535 mm
Weight (Net/Gross)	119/125 kg
Power	500 W
Power Supply	120V/220V/240V/380V/415V, 50Hz/60Hz



Biolab Scientific Ltd.

3660 Midland Avenue, Suite 300, Toronto, Ontario M1V 0B8, Canada
Email: contact@biolabscientific.com | Website: www.biolabscientific.com