



MUFFLE BOX FURNACE BFMF-1200-20

MUFFLE BOX FURNACE BFMF-1200-20

Designed for minimum space requirements, our muffle furnaces work effortlessly at high temperatures and give reliable results. Equipped with electronic controller and memory to store different programs, it makes the operation user friendly. Chambers are crafted for heavy duty operation and minimize heat loss.

Used in Ideal for material testing, ashing, annealing loss determination, chemical analysis, reaction studies, metallurgical research and rapid heat processes..

BFMF-1200-20 MUFFLE BOX FURNACE



- Programming with Easy-to-Understand Menu on 4-Line LCD Display
- Suitable for all Kinds of Processes such as Ash Analysis, Heat Treatment, Sintering, Preheating, Melting, Oxidation
- Durable Inner Chamber Made of Light Isolation Bricks
- Accurate Measurement and Temperature Control with K Type Thermocouple
- Homogeneous Heat Distribution
- Space-Saving in the Laboratory with Unique Insulation Design
- Low External Surface Temperature with Dual Layer Housing
- Heating Elements which are Selected and Designed According to Their Proper Working Temperatures and Providing Fast Heating of the Furnace
- Heating Element Protection with Quartz Tubes against the Effects of Harmful Gases
- Fan and Chimney System for Discharging Corrosive and Oxidizing Gases
- Optional Features such as Protective Gas Connection, Door Sensor, Second Thermocouple (Indicator)
- Lift-Up & Sideways Door Options

SPECIFICATIONS

Model	BFMF-1200-20
Capacity	20 L
Maximum Temperature	1200°C
Working Temperature	1200°C
Control Unit	B2
Controller Description	4x20 LCD / 4 Steps 2 Prog
Software Options	B2, E4, U8, S16
Control Accuracy	±1°C
Front Face Insulation Material	Ceramic Fire Brick
Door Insulation Material	Ceramic Fibre Board
Housing Material	Steel Sheet
Housing Coating	Epoxy Powder Coating
Chimney	Standard
Heating Element Protection	Quartz Tube
Lockable Door Handle	Sideways
Inner Insulation Material	Insulating Fire Brick
Heating Element Placement	Embedded into Brick Walls
Thermocouple Type	K Type
Heating Element Type	Fe-Cr-Al
Inner Dimension (WxDxH)	250x200x395 mm
Outer Dimension (WxDxH)	546x668x790 mm

Gross Dimensions (WxDxH)	606x950x728 mm
Net Weight	65 Kg
Gross Weight	85 Kg
Power	4200 W
Maximum Current	2×9.6 / 1×19.1 A
Electrical Connection	3 veya 1 Phase
Power Supply	220V / 50Hz
Note	Available model with capacity 7L, 10L, 40L, 60L



Biolab Scientific Ltd.

3660 Midland Avenue, Suite 300, Toronto, Ontario M1V 0B8, Canada
Email: contact@biolabscientific.com | Website: www.biolabscientific.com