



FRP FUME HOOD

FRP FUME HOOD BKL-701 BKL-702 BKL-703

FRP FUME HOOD



SPECIFICATIONS

Model	BKL-701	BKL-702	BKL-703
Internal Size (W*D*H)	950*670*1150mm	1250*670*1150mm	1550*670*1150mm
External Size (W*D*H)	1245*800*2300mm	1500*800*2300mm	1800*800*2300mm
Exhaust air volume	864-1296m³/h	1080-1620m³/h	1296-1944m³/h
Air Velocity	0.4-0.6 m/s		
Material	Mechanically molded flame-retardant FRP (Fiber Reinforced Polymer)		
WORK SURFACE	Epoxy resin board (optional phenolic or ceramic)		
Lighting	LED lamp with corrosion-resistant, sealed housing		
CONTROLLER	Intelligent button or touch screen		
ELECTRIC OUTLET	Flame-retardant PC with copper internal conductors		
Alt Name	FRP FUME HOOD		

FRP FUME HOOD BKJ-802

FRP FUME HOOD



1. Corrosion resistance: FRP has a wide range of corrosion resistance, it is suitable for acid gas, toxic and harmful gases and organic solvent gas and dust production operation post and occasions.
2. Operation table: 12.7mm thick phenolic resin board, acid and alkali resistance, moisture proof, anti shock.
3. Adjust door: two section type safety tempered glass, stepless balanced lifting, pulling up and down to stay in any position.
4. Lighting: fluorescent lamp light source and anti-corrosion, isolation light a

SPECIFICATIONS

Model	BKJ-802
Internal Size (W*D*H)	
External Size (W*D*H)	1500*850*2350mm
Exhaust Air Volume	1500~2000m ³ /h
Air Velocity	0.3~0.8m/s
Noise	≤60Db(A)
Sash	5mm thickness tempered glass
Worktop	Phenolic resin / Epoxy resin / Ceramic / Trespa / SUS / PP
Lighting	Full cover type LED lamp with 220V * 20W * 2
Operation Panel	Switch of Lighting,ON/OFF,Electric socket and Blower
Sink	PP sink, Epoxy resin sink
Electric Socket	Multi-functional type,220V/10A
Working Door Opening	800mm~1000mm
Alt Name	FRP Fume Hood

FEATURES

1. Corrosion resistance: FRP has a wide range of corrosion resistance, it is suitable for acid gas, toxic and harmful gases and organic solvent gas and dust production operation post and occasions.
2. Operation table: 12.7mm thick phenolic resin board, acid and alkali resistance, moisture proof, anti shock.
3. Adjust door: two section type safety tempered glass, stepless balanced lifting, pulling up and down to stay in any position.
4. Lighting: fluorescent lamp light source and anti-corrosion, isolation light and gas , table light is more than 400 lumens.
5. Operation panel: lighting switch, fan ON/OFF switch, 220V, 10A multi-function two sockets.
6. Light weight, high strength,FRP can withstand 80 °C temperature for a long time, short-term to 130 °C , FRP oxygen index is more than 30,belong to flame retardant materials.



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: info@biolabscientific.com | Website: www.biolabscientific.com