



AIR SHOWER BASB-103

AIR SHOWER BASB-103

AIR SHOWER



1. Photoelectric sensor, automatic blowing.
2. Adopt with circulation wind to ensure the cleanness of shower area under non-shower status.
3. Double doors by electric interlock.
4. LED display with adjustable blowing time (0~99s).
5. HEPA Filter, Class 100 cleanness.

SPECIFICATIONS

Model	BASB-103
External Size(W*D*H)	1500*2000*2050mm
Internal Size(W*D*H)	800*1900*1930mm
HEPA Filter	99.995% efficiency at 0.3μm
Spraying Wind Speed	25m/s
Air Shower Time	0~99s(adjustable)
No.of SS Nozzles	24
Fluorescent Lamp	12W*1
Consumption	2200W
Cabinet Material (Optional)	1. Full cold-rolled steel with powder coating.2. Internal stainless steel, external with cold-rolled steel.3. Full stainless steel.
Door Material (Optional)	1.Cold-rolled steel with powder coating.2. Stainless steel.
Chassis	Stainless steel.
Power Supply	AC220V±10%, 50/60Hz; 110V±10%, 60Hz
Gross Weight	700kg
Package Size(W*D*H)	1600*2200*2200mm
Alt Name	Air Shower



APPLICATIONS

Air shower is a necessary passage for people entering clean room in order to minimize the amount of particulate contaminant, to achieve workplace strict clean purification standards. Personnel move through the air shower while particulate contaminants are blown off by the clean high-speed air. Then the dust cannot be brought into clean area.



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada
Email: info@biolabscientific.com | Website: www.biolabscientific.com