



LABORATORY HIGH SPEED REFRIGERATED CENTRIFUGE BCBHR-201

LABORATORY HIGH SPEED REFRIGERATED CENTRIFUGE

BCBHR-201

TABLETOP HIGH SPEED REFRIGERATED CENTRIFUGE



1. Brushless DC frequency motor with simpler construction, more reliable performance, longer life and quietly running.
2. Imported compressors, fluorine-free, double cycle cooling, cold and hot alternating easily, environment pollution-free and precise in temperature control.
3. Microprocessor control, digital display in speed, temperature and time etc, touch by panel, running parameters can be edited and changed to be RCF.
4. Automatically electric lid lock, super speed, over temperature protection and imbalance protection. The centrifuge body is made of high quality steel, safe and reliable.
5. Rotor is connected to spindle by specialized taper sleeve, loading simple and quick, no direction, safe and reliable.
6. There are 10 kinds of acceleration and deceleration for your choice. 7.3 laye

SPECIFICATIONS

Model	BCBHR-201
Max speed	16000rpm
Max volume	6x100ml
Timer	1-9h59min
Dimension(HxDxW)	608x570x380mm
Speed accuracy	±20rpm
Temperature range	-20~40°C
Max RCF	20600xg
Noise	≤58dBA
Net weight	82KG
Power supply	AC 220V 50HZ 10A
Package	Wooden box
Temperature accuracy	±1°C
Alt Name	Tabletop High Speed Refrigerated Centrifuge

ACCESSORIES FOR PURCHASE

No	Name	Max speed(rpm)	Max capacity	Max RCF(xg)
1	Angle rotor	16000	12*1.5/2ml	17940
2	Angle rotor	14000	40*0.5ml	19970
3	Angle rotor	15000	24*1.5/2ml	20600
4	Angle rotor	13500	30*1.5/2ml	19340
5	Angle rotor	15000	16x5ml	19350
6	Angle rotor	14000	12x7ml	16370
7	Angle rotor	10000	12x15ml	11840
8	Angle rotor	12000	12x10ml	14510
9	Angle rotor	12000	8x20ml	14510
10	Angle rotor	12000	6x30ml	14000
11	Angle rotor	11000	6x50ml	13480
12	Angle rotor	10000	6x70ml	10810
13	Angle rotor	10000	4x100ml	10310
14	Angle rotor	10000	6x100ml	11380

15	Angle rotor	14000	6x10ml	16460
16	Angle rotor	15000	30x0.5ml	18510
17	Angle rotor	13000	48x1.5/2ml	17930
18	Bucket rotor	4000	2x3x48 well	2300
19	vertical rotor	16000	16x5ml	16540

FEATURES

- 1.Brushless DC frequency motor with simpler construction,more reliable performance,longer life and quietly running.
- 2.Imported compressors,fluorine-free, double cycle cooling, cold and hot alternating easily,environment pollution-free and precise in temperature control.
3. Microprocessor control, digital display in speed, temperature and time etc, touch by panel, running parameters can be edited and changed to be RCF.
4. Automatically electric lid lock, super speed, over temperature protection and imbalance protection. The centrifuge body is made of high quality steel, safe and reliable.
5. Rotor is connected to spindle by specialized taper sleeve, loading simple and quick, no direction, safe and reliable.
6. There are 10 kinds of acceleration and deceleration for your choice. 7.3 layers protection of steel structure, safe and reliable.
- 8.It is with CE certificate , ISO13485 & ISO9001



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada
 Email: info@biolabscientific.com | Website: www.biolabscientific.com