



## CLASS II BIOSAFETY CABINET BCBS-1101

# CLASS II BIOSAFETY CABINET BCBS-1101

EN CERTIFIED BIOLOGICAL SAFETY CABINET



1. 7-inch large touch color display: touch operation, real-time and clearer display of various values of the safety cabinet, dynamic air flow pattern diagram, fault alarm sound and light prompt.
2. The power-on password can be set to prevent mis-operation by irrelevant personnel.
3. Automatically adjust the wind speed.
4. Power-off memory, restore the state before power-off, and have a visual reminder to alarm.
5. Side windows on both sides for easy observation.
6. The operation area is integrally formed, which is easy to disassemble and clean.
7. A breeze speed sensor is equipped at the working area and the outer exhaust a

## SPECIFICATIONS

Model	BCBS-1101
External Size(W*D*H)	1087*800*2260mm
Internal Size(W*D*H)	980*600*650mm
Work Surface Height	750mm
Max Opening Height	500mm
Tested Opening	200mm
Airflow Volume: Inflow	370m <sup>3</sup> /h(218cfm)
Airflow Volume: Down flow	65%: 690 m <sup>3</sup> h(406cfm)
Airflow Volume: Exhaust	35%: 370m <sup>3</sup> /h(218cfm)
Front Window	Manual and electric, glass thickness> 5mm, anti-ultraviolet
ULPA Filter	2pcs, filtration efficiency for 0.12um particles 299.9995 %
Illumination	≥1000Lux
Noise	EN12469≤65dB
Display	Color Touch Screen
European Standard Socket	230V, 3A
Power Supply	AC 230V, 50/60Hz
Rated Power	1100W
Alarm	Alarm for abnormal wind speed, alarm for glass door not at safe height, alarm for abnormal power failure
Motor	AC single fan,Adjustable speed, high efficiency, low power
Material	Working Area: 304 stainless steel, side window glass;Frame and decorative plate: cold-rolled steel with anti-bacteria powder coating
LED Lamp	12W*2
UV Lamp	20W
Standard Accessory	Cabinet*1, Base stand*1, LED lamp*2, UV lamp*1, S.S. water tap*1, S.S. gas tap*1, Drain ball valve*1,European Standard Socket*2
Optional Accessory	Arm rest, Formalin fumigation sterilizer, Infrared sterilizer, Electric height adjustable base stand,S.S. water tap*1, S.S. gas tap*1, Remote control, Foot switch
Package Size (W*D*H)	1240*1060*1880mm
Gross Weight	270kg
Alt Name	EN Certified Biological Safety Cabinet

## FEATURES

1. 7-inch large touch color display: touch operation, real-time and clearer display of various values of the safety cabinet, dynamic air flow pattern diagram, fault alarm sound and light prompt.
2. The power-on password can be set to prevent mis-operation by irrelevant personnel.
3. Automatically adjust the wind speed.
4. Power-off memory, restore the state before power-off, and have a visual reminder to alarm.
5. Side windows on both sides for easy observation.
6. The operation area is integrally formed, which is easy to disassemble and clean.
7. A breeze speed sensor is equipped at the working area and the outer exhaust air outlet to detect the wind speed in real time.
8. It can be used both manually and electrically, and the glass door can be pulled down to close the front window when the power is off.
9. The cabinet is separated from the base. The height of the adjustable base can be customized.
10. Interlocking function: UV lamp and front window; UV lamp and fan, fluorescent lamp; fan and front window.
11. It has an appointment timing function, which can automatically set the timing of turning on, turning off and the running time of the UV lamp, fan, and socket.
12. The closing of the front window can double trigger the signal, so that the sterilization and disinfection function of the UV lamp can be turned on normally.
13. The cabinet is designed with a 10° inclination angle, which conforms to the principle of ergonomics, has a larger viewing angle, is easy to operate and is more user-friendly.
14. Anti-paper dust structure at the air inlet to prevent paper dust from entering the air cavity.
15. Split countertop is easier to clean.
16. One button front window lifting function.

Color Touch Screen, Touch operation, real-time and clearer display of various values and appointment timing function.



SS Water tap & Gas tap



Wind Speed Sensor



Stepper Motor



Work zone, made of 304 stainless steel, is surrounded by negative pressure.



Anti-paper dust structure



Footmaster Caster, Universal caster with brake and leveling feet.



European Standard Socket



UV Lamp, Emission of 253.7 nanometers for most efficient decontamination.



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)