



VERTICAL LAMINAR AIRFLOW BDL-3601

VERTICAL LAMINAR AIRFLOW BDL-3601

PP VERTICAL LAMINAR FLOW CABINET



1. Made of PP material, integrally welded
 2. Resistant to strong acid, alkali and strong corrosion
 3. With memory function in case of power-failure
 4. Interlock function: UV Lamp and blower, LED Lamp
 5. The work surface is seamlessly welded with 12mm thick PP plate, which is convenient for overall cleaning.
- LCD Display, airflow velocity, UV Timer, UV work time, system work time, real time.
UV Lamp, Emission of 254 nanometers for most efficient decontamination.
Waterproof Socket, 2 waterproof sockets are located inside the panel, for optimum convenience of using small devices inside the cabinet.
Footmaster Caster, Universal caster with brake and leveling feet

SPECIFICATIONS

Model	BDL-3601
External Size(W*D*H)	800*710*1800mm
Internal Size(W*D*H)	780*540*550mm
Work Surface Height	750mm
Material	Main Body: Made of porcelain white PP, thickness 8mm, resistant to strong acid, alkali and anti-corrosion Work Table: Seamlessly welded with 12mm thick PP plate
Front&Side Windows	5mm toughened glass, anti-UV, manual
Pre-filter	Polyester fiber, washable
Filter Size(W*D*H)	560*340*46mm
HEPA Filter	99.995% efficiency at 0.3µm
Airflow Velocity	0.3~0.5m/s
Noise	≤65dB
Max. Opening	400mm
UV Lamp	20W*1, Emission of 253.7 nanometers, with UV time
LED Lamp	8W
Illumination	≥350lx
Caster	Foot master caster
Waterproof Socket	Two, total load≤500W
Consumption	650W
Standard Accessory	UV lamp, Led lamp, Base stand, Waterproof socket*1
Power Supply	220V, 50/60Hz(Standard); 110V, 60Hz(Optional)
Package Size(W*D*H)	1000*900*1300mm
Gross Weight	90kg
Alt Name	PP Vertical Laminar Flow Cabinet


FEATURES

1. Made of PP material, integrally welded
2. Resistant to strong acid, alkali and strong corrosion
3. With memory function in case of power-failure
4. Interlock function: UV Lamp and blower, LED Lamp
5. The work surface is seamlessly welded with 12mm thick PP plate, which is convenient for overall cleaning.

LCD Display, airflow velocity, UV Timer, UV work time, system work time, real time.



UV Lamp, Emission of 254 nanometers for most efficient decontamination.



Waterproof Socket, 2 waterproof sockets are located inside the panel, for optimum convenience of using small devices inside the cabinet.



Footmaster Caster, Universal caster with brake and leveling feet



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada
Email: info@biolabscientific.com | Website: www.biolabscientific.com