



## WALK IN FUME HOOD BDL-4901

# WALK IN FUME HOOD BDL-4901

## FUME HOOD



1. The cabinet is designed with a vertical surface, the operation perspective is wide and more humanized.
2. Made of high quality cold rolled steel plate material, surface electrostatic spraying, with good finish.
3. The platform panel of the operation area of the fume hood is made of solid physical and chemical plate, which is resistant to acid and alkali corrosion and can be disassembled for easy cleaning (integral type).
4. The front window adopts 5mm thick tempered glass to better protect the safety of personnel and experiments.
5. Counterweight manual front window, height adjustable.
6. The base bracket and fuma castor integrated design, safely moved through the casters, also well fixed and levelled.

## SPECIFICATIONS


Model	BDL-4901
Number of Users	Single
Rated Power	95W (Not including socket load power, load power cannot exceed 500W)
Power Supply	220V±10%, 50Hz(Standard); 110V±10%, 60Hz(Optional)
Exhaust Volume	1225m <sup>3</sup> /h
Air Velocity	0.3m/s~0.8 m/s
Noise	≤65dB(A)
LED Lamp	4W
Max Opening	410mm(Integral Type)
Tabletop Height	810mm(Integral Type)
Standard Accessory	LED Lamp, National standard three core splash proof socket,
Optional Accessory	Base Stand, Bench physical and chemical board
Net Weight Desktop Type	60kg
Net Weight Integral Type	80kg
Gross Weight Desktop Type	78kg
Gross Weight Integral Type	100kg
External Size (W*D*H) Desktop Type	700*650*1050mm
External Size (W*D*H) Integral Type	700*650*1850mm
Internal Size(W*D*H)	580*510*687mm
Package Size (W*D*H) Desktop Type	1010*850*1250mm
Package size (W*D*H) Integral Type	1010*850*1250mm
Alt Name	Fume Hood

## FEATURES

1. The cabinet is designed with a vertical surface, the operation perspective is wide and more humanized.
2. Made of high quality cold rolled steel plate material, surface electrostatic spraying, with good finish.
3. The platform panel of the operation area of the fume hood is made of solid physical and chemical plate, which is resistant to acid and alkali corrosion and can be disassembled for easy cleaning (integral type).
4. The front window adopts 5mm thick tempered glass to better protect the safety of personnel and experiments.
5. Counterweight manual front window, height adjustable.

6. The base bracket and fuma castor integrated design, safely moved through the casters, also well fixed and levelled.
7. Equipped with PP centrifugal fan, large air volume, low noise, long service life, easy installation.
8. The fan can be stepless speed regulation, the function button is push-button switch, stable performance.
9. The side of the cabinet body is equipped with lifting handles to facilitate carrying.

UV Lamp



Footmaster Caster, Universal Caster with Brake and Leveling Feet



Waterproof Socket



Base Stand Optional



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada  
Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)