




CLASS II BIOSAFETY CABINET BEM1B1 (BCBS-1103)

CLASS II BIOSAFETY CABINET BEM1B1

EN CERTIFIED BIOLOGICAL SAFETY CABINET

Three protection: operator, sample and environment. Airflow system: 70% air recirculations 30% air exhaust Cabinet is suitable for working with microbiological research in the absence of volatile or toxic chemicals and radionuclide.



Color Touch Screen, Touch operation, real-time and clearer display of various values and appointment timing function.

Anti- paper dust structure

Wind Speed Sensor

Stepper Motor

Work zone, made of 304 stainless steel, is surrounded by negative pressure.

Footmaster Caster, Universal caster with brake and leveling feet.

European Standard Socket

UV Lamp, Emission of 253.7 nanometers for most efficient decontamination.

1. 7-inch large touch color display: touch operation, real-time and clearer display of various values of the safety cabinet, dynamic air flow pattern diagram, fault alarm sound and light prompt.

SPECIFICATIONS

Model	BEM1B1
Old Model	BCBS-1103
External Size(W*D*H)	700*700*2000mm
Internal Size(W*D*H)	600*500*540mm
Work Surface Height	750mm
Max Opening Height	350mm
Safe OperationOpening Height	200mm
Airflow Volume: Inflow	230m3/h(135cfm)
Airflow Volume: Down flow	65%: 428 m3/h(252cfm)
Airflow Volume: Exhaust	35%: 230m3/h(135cfm)
Front Window	Manual and electric, glass thickness> 5mm, anti-ultraviolet
ULPA Filter	2pcs, filtration efficiency for 0.12um particles≥99.9995%
Illumination	>1000Lux
Noise	EN12469<65dB
Display	Color Touch Screen
European Standard Socket	230V, 3A
Power Supply	AC 230V, 50/60Hz
Rated Power	950W
Alarm	Alarm for abnormal wind speed, alarm for glass door not at safe height, alarm for abnormal power failure
Motor	DC single fanAdjustable speed, high efficiency, low power
Material	Working Area: 304 stainless steel, side window glass;Frame and decorative plate: cold-rolled steel with anti-bacteria powder coating
LED Lamp	8W*2
UV Lamp	15W

Standard Accessory	Cabinet*1, Base stand*1, LED lamp*2, UV lamp*1, Drain ball valve*1, European Standard Socket*2
Optional Accessory	Arm rest, Formalin fumigation sterilizer, Infrared sterilizer S.S. water tap*2, S.S. gas tap*2
Package Size (W*D*H)	850*880*1550mm
Gross Weight	170kg
Alt Name	EN Certified Biological Safety Cabinet

FEATURES

Color Touch Screen, Touch operation, real-time and clearer display of various values and appointment timing function.



Anti- paper dust structure



Wind Speed Sensor



Stepper Motor



Work zone, made of 304 stainless steel, is surrounded by negative pressure.



Footmaster Caster, Universal caster with brake and leveling feet.



European Standard Socket



UV Lamp, Emission of 253.7 nanometers for most efficient decontamination.



1. 7-inch large touch color display: touch operation, real-time and clearer display of various values of the safety cabinet, dynamic air flow pattern diagram, fault alarm sound and light prompt.
2. The power-on password can be set to prevent mis-operation by irrelevant personnel.
3. Automatically adjust the wind speed.
4. Power-off memory, restore the state before power-off, and have a visual reminder to alarm.
5. Side windows on both sides for easy observation.
6. The operation area is integrally formed, which is easy to disassemble and clean.
7. Abreeze speed sensor is equipped at the working area and the outer exhaust air outlet to detect the wind speed in real time.
8. It can be used both manually and electrically, and the glass door can be pulled down to close the front window when the power is off.
9. The cabinet is separated from the base. The height of the adjustable base can be customized.
10. Interlocking function: UV lamp and front window; UV lamp and fan, fluorescent lamp; fan and front window.
11. It has an appointment timing function, which can automatically set the timing of turning on, turning off and the running time of the UV lamp, fan, and socket.
12. The closing of the front window can double trigger the signal, so that the sterilization and disinfection function of the UV lamp can be turned on normally.
13. Anti-paper dust structure at the air inlet to prevent paper dust from entering the air cavity.
14. Split countertop is easier to clean.
15. One button front window lifting function.



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada
Email: info@biolabscientific.com | Website: www.biolabscientific.com