



COMPOUNDING HOOD BEM1BL4 (BCHL-402)

COMPOUNDING HOOD BEM1BL4

COMPOUNDING HOOD



There are two types:

- Positive pressure in work area only protects sample.

LCD Display

Active Carbon Filter

Acrylic Front Window

SPECIFICATIONS

Model	BEM1BL4
Old Model	BCHL-402
External Size (W*D*H)mm	600*580*1060mm
Internal Size (W*D*H)	580*520*610mm
Display	LCD Display
Airflow Velocity	0.3~0.8m/s
Material Main body	Cold-steel with anti-rust powder coating
Material Work table	304 stainless steel
Pre-Filter	Polyester fiber,
Filter	Active Carbon Filter
Noise	≤60dB
Front Window	Manual, acrylic material
Max Opening	590mm
LED Lamp	4W*1
UV Lamp	8W*1 Emission of 253.7 nanometers
Consumption	150W
Power Supply	AC220V±10%, 50/60Hz; 110V±10%, 60Hz;
Standard Accessory	Active carbon filter, LED lamp, UV lamp*2, Waterproof socket.
Optional Accessory	Base stand
Gross Weight	90kg
Package Size (W*D*H)mm	760*740*1280
Alt Name	Compounding Hood



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: info@biolabscientific.com | Website: www.biolabscientific.com