



COMPOUNDING HOOD BEM1BL7 (BCHL-405)

COMPOUNDING HOOD BEM1BL7

COMPOUNDING HOOD



There are two types:

- Positive pressure in work area only protects sample.

LED Display

Active Carbon Filter, HEPA Filter

Acrylic Front Window

SPECIFICATIONS

Model	BEM1BL7
Old Model	BCHL-405
External Size (W*D*H)mm	1000*620*1150mm
Internal Size (W*D*H)	940*550*700mm
Display	LED Display
Airflow Velocity	0.3~0.8m/s
Material Main body	Cold-steel with anti-bacterial powder coating
Material Work table	Solid physicochemical steel plate
Pre-Filter	Polyester fiber
Filter	Active Carbon Filter, HEPA Filter
Noise	≤60dB
Front Window	Manual, acrylic material
Max Opening	660mm
LED Lamp	12W*1
UV Lamp	15W*1 (optional) Emission of 253.7 nanometers
Consumption	200W
Power Supply	AC220V±10%, 50/60Hz; 110V±10%, 60Hz;
Standard Accessory	Active carbon filter, HEPA filter, 4 meters PVC exhaust duct, Diameter: 250mm.
Optional Accessory	Base Stand, UV Lamp*2
Gross Weight	145kg
Package Size (W*D*H)mm	1140*740*1340
Alt Name	Compounding Hood

FEATURES


There are two types:

- Positive pressure in work area only protects sample.

LED Display

Active Carbon Filter, HEPA Filter

Acrylic Front Window



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: info@biolabscientific.com | Website: www.biolabscientific.com