



DUCTED FUME HOOD BEM1BP3 (BFSD-203)

DUCTED FUME HOOD BEM1BP3

DUCTED FUME HOOD



- LED Display
- Waterproof Socket
- Water&Gas Remote Control
- Double Layer, 1.2mm sheet metal surface, melamine board inward.
- 1. UV lamp for sterilization.
- 2. resistant to weak acid and alkali.
- 3. Adjustable air speed: 9 levels.
- 4. Motorized front window, height adjustable.
- 5. Microprocessor control system, LED display.
- 6. With memory function in case of power-failure.

SPECIFICATIONS

| | |
|-----------------------|---|
| Model | BEM1BP3 |
| Old Model | BFSD-203 |
| External Size (W*D*H) | 1540*800*2200mm |
| Internal Size (W*D*H) | 1320*670*730mm |
| Work Surface Height | 850mm |
| Max Opening | 520mm |
| Air Velocity | 0.3~0.8m/s. |
| Noise | ≤68dB |
| Exhaust Duct | PVC, Standard length: 4 meters.Φ300mm |
| LED Lamp | 16W*1 |
| UV Lamp | Emission of 253.7 nanometers for most efficient decontamination |
| Blower | Built-in centrifugal blower; Speed adjustable |
| Front Window | 5mm toughened glass; Motorized; Height adjustable |
| Power Supply | AC220±10%, 50/60Hz; 110V±10%, 60Hz |
| Consumption | 500W |
| Exhaust Air Volume | 950 m³/h |
| Material Exterior | Cold-rolled steel with anti-bacteria powder coating. |
| Material Interior | 'Compact laminate board with good acid and alkali resistance function |
| Material Work Table | Chemical resistant phenolic resin |
| Standard Accessories | UV lamp*2, LED lamp, Water tap, Gas tap, Water sink, Base cabinetTotal load of 2 waterproof sockets: 500W4.3 meter PVC exhaust duct, pipe strap*2 |
| Optional Accessory | Active carbon filter, HEPA filter |
| Gross Weight | 350kg |
| Package Main Body | 1690*990*1690mm |
| Package Base Cabinet | 1690*990*900mm |
| Alt Name | Ducted Fume Hood |

FEATURES

LED Display



Waterproof Socket



Water&Gas Remote Control



Double Layer, 1.2mm sheet metal surface, melamine board inward.



1. UV lamp for sterilization.
2. resistant to weak acid and alkali.
3. Adjustable air speed: 9 levels.
4. Motorized front window, height adjustable.
5. Microprocessor control system, LED display.
6. With memory function in case of power-failure.



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: info@biolabscientific.com | Website: www.biolabscientific.com