



DUCTED FUME HOOD BEM1BS3 (BFSD-403)

DUCTED FUME HOOD BEM1BS3

DUCTED PP FUME HOOD



- LED Display
- Waterproof Socket
- Water&Gas Remote Control
- PP Sink, resistant to acid, alkali and anti-corrosion
- 1. It is safer to use anti-corrosive water tap.
- 2. Microprocessor control system, LED display.
- 3. With memory function in case of power-failure.
- 4. Made of porcelain white PP, resistant to acid, alkali and anti-corrosion.
- 5. Front window which is made of 5mm thick transparent toughened glass maximize light and visibility inside the fume hood, providing a bright and open working environment.

SPECIFICATIONS

Model	BEM1BS3
Old Model	BFSD-403
External Size (W*D*H)	1547*800*2450mm
Internal Size (W*D*H)	1287*560*700mm
'Work Surface Height	820mm
Max Opening	740mm
Air Velocity	0.3~0.8m/s
Noise	≤68dB
Exhaust Duct	4.3 meters, φ250mm
LED Lamp	22w*2
Blower	Built-in PP centrifugal blower (2 blowers for FH1800(P) only); Speed adjustable
Front Window	Resistant to acid and alkali, Manual, 5Smm toughened glass, height adjustable
Power Supply	AC220V±10%, 50/60Hz; 110V±10%, 60Hz
Consumption	500W
Material Main Body	Made of Porcelain white PP, thickness 8mm, resistant to strong acid, alkali and anti-corrosion
Material Work Table	Chemical resistant phenolic resin
Standard Accessory	LED light;Work table:Chemical resistant phenolic resin; 4.3 meters PVC duct (2 Pcs of 4.3 meters PVC duct for FH1800(P) only), Diameter: 250mm;Pipe strap*2(4 Pcs for FH1800(P) only); RVV power cord (3*1.0mm²*3000mm); Base cabinet; Waterproof socket*2; Tail insert;Water tap(PP); Gas tap(PP); Water Sink;PP centrifugal blower*1(2 for FH1800(P)
Gross weight Main Body	180kg
Gross weight Base Cabinet	114kg or 102kg(Spllicable)
Package Size (W*D*H) Main Body	1688*938*1612mm
Package Size (W*D*H) Base Cabinet	1688*888*1000mm or 1700*1000*450mm(Spllicable)
Alt Name	Ducted PP Fume Hood

FEATURES

LED Display



Waterproof Socket



Water&Gas Remote Control



PP Sink, resistant to acid, alkali and anti-corrosion



1. It is safer to use anti-corrosive water tap.
2. Microprocessor control system, LED display.
3. With memory function in case of power-failure.
4. Made of porcelain white PP, resistant to acid, alkali and anti-corrosion.
5. Front window which is made of 5mm thick transparent toughened glass maximize light and visibility inside the fume hood, providing a bright and open working environment.



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: info@biolabscientific.com | Website: www.biolabscientific.com