



## DUCTLESS FUME HOOD BEM1BW1

# DUCTLESS FUME HOOD BEM1BW1

## DUCTLESS FUME HOOD



5 inch Touch Screen  
Oil Proof Explosion, Proof Light  
Waterproof Socket  
Marble Countertops

1. It meets the acceptance criteria of the platform and can meet the accuracy of the balance use level of one hundred thousand.
2. LCD Touch screen control panel, easy to operate.
3. With memory function in case of power-failure
4. 8°slope front ergonomics design, fatigue-free working posture.
5. Temperature and humidity sensors, can detect indoor temperature and humidity.
6. Inside and outside probe, detect indoor air pollution and filter conditions.
7. Three side transparent Acrylic windows, front window reversal design, easy to

## SPECIFICATIONS

Model	BEM1BW1
External Size(W*D*H)	1230*830*2120mm
Instrument Size(W*D*H)	1110*740*700mm
Work Surface Height	880mm
Max Opening	650mm
Air Velocity	0.25~0.35m/s.
Airflow Volume	136m³/h
Noise	≤58dB(A)
Fluorescent Lamp	12W*2
Blower	Built-in blower
Front Window	Acrylic window ;Manual;Reversal design
Consumption	400w
Power Supply	AC220V±10%, 50Hz/60Hz; 110V±10%, 60Hz
Material Exterior	1.0mm cold rolled steel sheet, electrostatic spraying
Material Side Window	Acrylic window
Material Work table	Marble countertops
HEPA Filter	1 pcs
Optional Accessory	UV lamp
Net/Gross Weight	270/320kg
Package Size Main Body	1380*1040*1490mm
Package Size Base Cabinet	1380*1040*1060mm
Alt Name	Ductless Fume Hood

## FEATURES

5 inch Touch Screen



Oil Proof Explosion, Proof Light



Waterproof Socket



Marble Countertops



1. It meets the acceptance criteria of the platform and can meet the accuracy of the balance use level of one hundred thousand.
2. LCD Touch screen control panel, easy to operate.
3. With memory function in case of power-failure
4. 8°slope front ergonomics design, fatigue-free working posture.
5. Temperature and humidity sensors, can detect indoor temperature and humidity.
6. Inside and outside probe,detect indoor air pollution and filter conditions.
7. Three side transparent Acrylic windows, front window reversal design,easy to operate.
8. The operating area countertop adopts marble countertop, which can be disassembled for easy cleaning.
9. Electronic control system, anti-overload, anti-electric shock,stable performance, long service life.



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)