



WALK IN FUME HOOD BEM1CA2 (BFSD-802)

WALK IN FUME HOOD BEM1CA2

WALK-IN FUME HOOD



Water Sink

Water & Gas Remote, Control Valve

Water & Gas Tap

Application

Application

1. With memory function in case of power-failure.

2. Operators are available to walk into the fume hood to operate if need.

3. Large room exhaust system, suitable for large laboratory instruments and equipment.

SPECIFICATIONS

Model	BEM1CA2
Old Model	BFSD-802
External Size (W*D*H)	1500*800*2250mm
Internal Size (W*D*H)	1280*550*1670mm
Max Opening	1300mm
Exhaust Airflow Volume	1500m ³ /h
Inflow Air Velocity	0.3~0.8m/s.
Noise	≤62dB
Vibration	Amplitude≤5μm
Illumination	≥800Lux
LED Lamp	16W*2
Power Supply	AC220V±10%, 50/60Hz; 110V±10%, 60Hz
Consumption	500W
Front Window	Manual, 5Smm toughened glass,height adjustable
Material Exterior	1.0mm cold-rolled steel with bacteria powder coating.
Material Interior	Compact laminate board with good acid and alkali resistance function
Standard Accessory	External blower , LED lamp, Water tap, Gas tap, PP cup sink, Remote control water valve, Remote control gas valve, Waterproof sockets*4, 4.3 meters Φ300mm PVC exhaust duct
Sockets	Total load of 4 waterproof sockets: ≤500W
Package Size (W*D*H) Main Body	1710*1050*2450mm
Package Size (W*D*H) Exhaust Blower	1040*890*710mm
Gross Wight	340KG
Alt Name	Walk-in Fume Hood

FEATURES

Water Sink



Water & Gas Remote, Control Valve



Water & Gas Tap



Application



Application



1. With memory function in case of power-failure.
2. Operators are available to walk into the fume hood to operate if need.
3. Large room exhaust system, suitable for large laboratory instruments and equipment.



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada
Email: info@biolabscientific.com | Website: www.biolabscientific.com