



## FFU (FAN FILTER UNIT) BEM1CC2 (BFSD-902)

# FFU (FAN FILTER UNIT) BEM1CC2

FFU (FAN FILTER UNIT)



1. FFU shell and HEPA filter adopt split design, easy to install and replace.
2. Microprocessor control system, energy-saving and low noise.
3. Long service-life blower, up to 100,000 hours, maintenance-free and small vibration.
4. Suitable for using separately or connecting together for assembly line.
5. Made of aluminium coated zinc plate, anti-corrosion, rust-proof and light weight

## SPECIFICATIONS

Model	BEM1CC2
Old Model	BFSD-902
External Size(W*D*H)	1175*575*380 mm
Air Velocity	0.45m/s±20%
HEPA Filter	99.999% efficiency at 0.3µm
HEPA Filter Size(W*D*H)	1170*69*570mm
Blower	Built-in centrifugal blower
Noise	≤60dB
Consumption	110W
Power Supply	AC220V±10%, 50/60Hz; 110V±10%, 50/60Hz
Shell Material	Aluminium coated zinc plate
Gross Weight	70 kg
Package Size(W*D*H)	1335*540*800mm
Alt Name	FFU (Fan Filter Unit)



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)