



**DOUBLE ADJUSTABLE FREQUENCIES  
ULTRASONIC CLEANER BEM1CR5**

# DOUBLE ADJUSTABLE FREQUENCIES ULTRASONIC CLEANER

## BEM1CR5

### DOUBLE ADJUSTABLE FREQUENCIES ULTRASONIC CLEANER

The Double Adjustable Frequencies Type device is a versatile equipment commonly used in applications requiring precise frequency modulation for various industrial, medical, and research purposes.



1. Over-voltage and over-current protection.
2. Standard: 1pc of basket, 1pc of lid.
3. Low-level water protection.
4. Fully microprocessor controlled and programmable.
5. Digital display, easy setting for time and temperature.
6. Time and temperature real-time display.

## SPECIFICATIONS

Model	BEM1CR5
Capacity (L)	6
Adjustable Ultrasonic Frequency (KHz)	45/80
Time Range / Heating Temp	1~480min / RT~80°C
Ultrasonic Power (W)	200
Heating Power (W)	400
Tank Size (L*W*H mm)	300*150*150
Packing Size (L*W*H mm)	445*250*430
Gross Weight (kg)	9.5
Standard Power Supply	-
Alt Name	Double Adjustable Frequencies Ultrasonic Cleaner



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)