



HORIZONTAL LAMINAR AIRFLOW BEM1Y3 (BLHZ-202)

HORIZONTAL LAMINAR AIRFLOW BEM1Y3

ETL CERTIFIED HORIZONTAL LAMINAR FLOW CABINET



Stainless Steel L.V., Bar with 10 hooks
Waterproof Socket, America Standard
Footmaster Caster, Universal caster with brake and leveling feet
Wind Speed Sensor, Direct measurement of wind speed
1. ETL certification, Satisfy North American market.
2. With memory function in case of power-failure.
3. Audio and visual alarm (Abnormal airflow velocity).

SPECIFICATIONS

Model	BEM1Y3
Old Model	BLHZ-202
External Size(W*D*H)	1500*810*(1720~1980)mm
Internal Size(W*D*H)	1400*500*600mm
Work Surface Height	750~1010mm
Max Opening	440mm
Display	LCD Display
Airflow Velocity	80~99fpm
Material	Working area: 304 stainless Steel.Main Body: Cold-rolled steel with anti-bacteria powder coating.Front Window: 5 mm toughened glass, anti-UV.
Pre-Filter	Polyester fiber
HEPA Filter	HEPA Filter One,99.995% efficiency at 0.3 μm
Noise	≤65dB(A)
Illumination	≥300lx
Waterproof Sockets	One socket (Double type), America standard, Max.Power: 500W
Power Supply	103.5~126.5V, 60Hz, 10A
Consumption	950W
LED Lamp	18W*1
Standard Accessory	Manually height adjustable base stand,LED lamp, wind speed sensor, waterproof Socket, Stainless steel I.V.Bar with 10 hooks.
Optional Accessory	UV lamp
Package Size (W*D*H)	1640*1090*1250mm
Gross Weight	265kg
Alt Name	ETL Certified Horizontal Laminar Flow Cabinet

FEATURES

Stainless Steel L.V., Bar with 10 hooks



Waterproof Socket, America Standard



Footmaster Caster, Universal caster with brake and leveling feet



Wind Speed Sensor, Direct measurement of wind speed



1. ETL certification, Satisfy North American market.
2. With memory function in case of power-failure.
3. Audio and visual alarm (Abnormal airflow velocity).



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: info@biolabscientific.com | Website: www.biolabscientific.com