



## ULTRASONIC CLEANER BEM2M10 (BULC-910)

# ULTRASONIC CLEANER BEM2M10

## ULTRASONIC CLEANER

Ultrasonic cleaner is a non-polluting, non-damaging, multi-purpose cleaning equipment. It not only has a powerful cleaning effect on objects with complex shapes, but also accelerates dissolution and emulsification. Ultrasonic cleaner has the unparalleled advantages of other physical cleaning or chemical cleaning, and is widely used in service industry, electronics industry, pharmaceutical industry, laboratory, machinery industry, cemented carbide industry, chemical industry and other fields.



1. Standard accessories: soundproof cover, basket, PVC pipe.
2. The shell and inner cavity are made of 304 stainless steel, which is anti-corrosion.

## SPECIFICATIONS

|                          |                          |
|--------------------------|--------------------------|
| Model                    | BEM2M10                  |
| Old Model                | BULC-910                 |
| Capacity (L)             | 30                       |
| Ultrasonic Frequency     | single frequency, 40 kHz |
| Time Range/Heating Temp. | 1~60min/RT~80°C          |
| Ultrasonic Power (W)     | 600                      |
| Heating Power (W)        | 500                      |
| Power Supply             | AC220V, 50Hz             |
| Tank Size(mm)            | 500*300*200              |
| External Size(mm)        | 530*330*350              |
| Packing Size(mm)         | 640*400*400              |
| Gross Weight(kg)         | 15                       |
| Alt Name                 | Ultrasonic Cleaner       |



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)