



ULTRASONIC CLEANER BEM2M4 (BULC-904)

ULTRASONIC CLEANER BEM2M4

ULTRASONIC CLEANER

Ultrasonic cleaner is a non-polluting, non-damaging, multi-purpose cleaning equipment. It not only has a powerful cleaning effect on objects with complex shapes, but also accelerates dissolution and emulsification. Ultrasonic cleaner has the unparalleled advantages of other physical cleaning or chemical cleaning, and is widely used in service industry, electronics industry, pharmaceutical industry, laboratory, machinery industry, cemented carbide industry, chemical industry and other fields.



1. Standard accessories: soundproof cover, basket, PVC pipe.
2. The shell and inner cavity are made of 304 stainless steel, which is anti-corrosion.
3. LED display

SPECIFICATIONS

Model	BEM2M4
Old Model	BULC-904
Capacity (L)	22.5
Ultrasonic Frequency	single frequency, 40 kHz
Time Range/Heating Temp.	1~99min/RT~80°C
Ultrasonic Power (W)	480
Heating Power (W)	500
Power Supply	AC220V, 50Hz
Tank Size(mm)	500*300*150
External Size(mm)	530*330*310
Packing Size(mm)	640*400*400
Gross Weight(kg)	13
Alt Name	Ultrasonic Cleaner



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: info@biolabscientific.com | Website: www.biolabscientific.com