


## ULTRASONIC CLEANER BEM2N5 (BULC-915)

# ULTRASONIC CLEANER BEM2N5

## ULTRASONIC CLEANER

Ultrasonic cleaner is a non-polluting, non-damaging, multi-purpose cleaning equipment. It not only has a powerful cleaning effect on objects with complex shapes, but also accelerates dissolution and emulsification. Ultrasonic cleaner has the unparalleled advantages of other physical cleaning or chemical cleaning, and is widely used in service industry, electronics industry, laboratory, machinery industry, cemented carbide industry, chemical industry and other fields.



1. Standard accessories: 1pc of soundproof cover, 1pc of basket, 1pc of PVC pipe.
2. The shell and inner cavity are made of 304 stainless steel, which is anti-corrosion.
3. LED display

## SPECIFICATIONS

Model	BEM2N5
Old Model	BULC-915
Capacity (L)	30
Ultrasonic Frequency	Double frequency, 28/40kHz
Time Range/Heating Temperature	1~99min/RT~80°C
Ultrasonic Power	600W
Heating Power	500W
Power Supply	220V, 50Hz
Tank Size(mm)	500*300*200
External Size(mm)	530*330*350
Packing Size(mm)	640*415*425
Gross Weight(kg)	17
Alt Name	Ultrasonic Cleaner



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)