



## OVERHEAD STIRRER BER1BP4

# OVERHEAD STIRRER BER1BP4

## OVERHEAD STIRRER



1. Stainless steel head restraints, more durable.
2. Digital display model, stirring has three modes: positive, reverse, positive and negative alternating.
3. Digital type: brushless motor.
1. Stainless steel head restraints, more durable.
2. Digital display model, stirring has three modes: positive, reverse, positive and negative alternating.
3. Digital type: brushless motor.
4. It is new big power type, high torque, can be used for mixing mud.

## SPECIFICATIONS

Model	BER1BP4
Function	
Max. Volume (L)	40
Digital	LCD
Speed (r.p.m)	100~2500
Working Time	Continuous
Minimum Resolution (r.p.m)	100
Structure	
Exterior	Plastic shell
Driving Mode	Motor
Motor Power (kW)	0.12
Controller	
Continuous Operation	Yes
Setting Mode	Digital
Speed Display Mode	Digital
Timer	Yes
Max. Viscosity(Mpas)	50000
Specification	
Exterior Size (W*L*H)(mm)	115x95x240
Packing Size (W*L*H)(mm)	400x250x210
Plate Size (mm)	200x300
Plate Load	50KG
Power Supply (50/60Hz)	100~240V
Current Rating	8/9
Alt Name	Overhead Stirrer



## APPLICATIONS

Large capacity mechanical mixing equipment.



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)