



WATER DISTILLER BER1CN1

WATER DISTILLER BER1CN1

STAINLESS STEEL WATER DISTILLER (AUTOMATIC CONTROL TYPE)



1. The whole shell is designed in stainless steel, and the evaporation tank, condenser and heater are all made of stainless steel, which are resistant to corrosion and aging.
2. With water shortage protection function, when the liquid level is too low, it will automatically alarm and quickly cut off the heating, to ensure that the heater will not burn out, it is easy to operate, safe and reliable.
3. Automatic water replenishment function, when the cooling water is restored to supply water, it will automatically enter the evaporation bucket, to ensure that the float switch automatically controls the power supply, and automatically restore the output of distilled water.

SPECIFICATIONS

Model	BER1CN1
Voltage(V)	220
Output(L/H)	≥5
Heating Power(kw)	4.5
G.W(kg)	9.5
N.W(kg)	6
Exterior Size (DiaxH) mm	Φ 305x730
Packing Size (LxWxH) mm	380x350x870
Alt Name	Stainless Steel Water Distiller

APPLICATIONS

This product uses tap water as the source water and uses electric heating distillation method to produce distilled water, which is suitable for medical treatment, chemical industry, scientific research , laboratories, etc.



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: info@biolabscientific.com | Website: www.biolabscientific.com