



WATER DISTILLER BER1CN2

WATER DISTILLER BER1CN2

STAINLESS STEEL WATER DISTILLER (AUTOMATIC CONTROL TYPE)



1. The whole shell is designed in stainless steel, and the evaporation tank, condenser and heater are all made of stainless steel, which are resistant to corrosion and aging.
2. With water shortage protection function, when the liquid level is too low, it will automatically alarm and quickly cut off the heating, to ensure that the heater will not burn out, it is easy to operate, safe and reliable.
3. Automatic water replenishment function, when the cooling water is restored to supply water, it will automatically enter the evaporation bucket, to ensure that the float switch automatically controls the power supply, and automatically restore the output of distilled water.

SPECIFICATIONS

Model	BER1CN2
Voltage(V)	380
Output(L/H)	≥10
Heating Power(kw)	7.5
G.W(kg)	10.5
N.W(kg)	7.5
Exterior Size (DiaxH) mm	Φ 335x830
Packing Size (LxWxH) mm	390x350x900
Alt Name	Stainless Steel Water Distiller

APPLICATIONS

This product uses tap water as the source water and uses electric heating distillation method to produce distilled water, which is suitable for medical treatment, chemical industry, scientific research , laboratories, etc.



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: info@biolabscientific.com | Website: www.biolabscientific.com