



## -86°C ULT FREEZER BEZ2E1

# -86Â°C ULT FREEZER BEZ2E1

-86Â°C ULTRA-LOW FREEZER QUICKCOOL



Accurate temperature controller, setting temperature range is -40 to -86Â°C, accuracy is 0.1 Â°C.

Suggested ambient temperature: +10 to 32Â°C.

Stainless steel inner chamber for friendly use and easy cleaning.

Brand compressor to ensure excellent stability of the cooling system.

Patented refrigeration technology, high-efficiency mixed gas for the cooling system.

Security

Safety door lock to prevent unauthorized access.

Visual and audible alarm system: High/low temperature, sensor failure, controller error.

Power failure protection: turn-on delay of the cooling system after power failur

## SPECIFICATIONS

Model	BEZ2E1
Temperature Range	-40 ~ -86Â°C
Ambient Temperature	10~32Â°C
Capacity (L / Cu.Ft.)	305 / 10.77
Interior Dimensions (WxDxH)	1190x448x640 mm
Exterior Dimensions (WxDxH)	1394x752x900 mm
Weight	115 kgs
Noise	53 dB
Controller	Microprocessor
Display	Digital
Sensor	PTC
Voltage & Frequency	220VÂ±10%, 50/60Hz
Power	460 W
Electric Current	2.09 A
Power Consumption (kWh/24h)	7.6
High/Low Temp Alarm	Yes
Sensor Error Alarm	Yes
Controller Error Alarm	Yes
Power Failure Alarm	Optional
Refrigeration Type	Direct Cooling
Defrost	Manual
Compressor (Brand/pcs)	SECOP / 1
Refrigerant / Weight	R400A / 270g
Door (pcs)	Foamed Solid Door / 1
Interior Cabinet Material	304 Stainless Steel
Exterior Cabinet Material	Coated Steel
Insulation Material	PURF (â‰¥100mm)
Door Lock	Yes
Test Hole (pcs)	1
Castors (pcs)	4
Remote Alarm Port	Optional

Temperature Datalogger	Optional
Protective Gloves	Optional
Basket (pcs)	Optional
Package	Carton box with pallet
Shipping Weight	142 kgs
Shipping Size (WxDxH)	1500x830x1080 mm
Shipping Volume	1.34 CBM
Alt Name	-86°C Ultra-low Freezer QuickCool

## FEATURES

Accurate temperature controller, setting temperature range is -40 to -86°C, accuracy is 0.1 °C.

Suggested ambient temperature: +10 to 32°C.

Stainless steel inner chamber for friendly use and easy cleaning.

Brand compressor to ensure excellent stability of the cooling system.

Patented refrigeration technology, high-efficiency mixed gas for the cooling system.

### Security

Safety door lock to prevent unauthorized access.

Visual and audible alarm system: High/low temperature, sensor failure, controller error.

Power failure protection: turn-on delay of the cooling system after power failure.

Controller error protection: the cooling system will remember the normal working cycle and keep working depending on this memory when the controller or two sensors failed.

### Humanized design

Casters with stoppers for easy moving and fixation.

Special-designed service-free drainage system.

## APPLICATIONS

The -86°C ultra-low temperature freezers are designed for the long-term preservation of viruses, germs, vaccines, biological tissues and organs, special food, medicines, reagents, etc.



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)