



## TUBE SEALER BFH-601

# TUBE SEALER BFH-601

HORIZONTAL INTELLIGENT TUBE SEALER



Triple Heat Dissipation, Continuous heat Sealing Capability  
Wide Sealing Surface, Maximum Heat Sealing tube diameter:6 mm  
No Preheating Required, Ready to use startup  
Splash Protection plate, Metal Shielding Casing for safety.

## SPECIFICATIONS

Model	BFH-601
Heat Sealing Time:	0.5-2s
Indicator Light Colors:	Red/Blue
Grounding Protection:	Class I
Power Consumption:	250W during operation,10W in stand by
Weight:	5.5 kg
Operating Temperature:	0-40°C
Heat sealing TubeOuter Diameter:	2-6mm
RF frequency	40.68MHz
Power supply:	100V~120V/220V-240V AC
Dimensions:	175X155X315mm
Fuse:	3A/250VAC 5*20mm
Storage Temperature:	-20~7°C
Alt Name	Horizontal Intelligent Tube Sealer

## FEATURES

Triple Heat Dissipation, Continuous heat Sealing Capability



Wide Sealing Surface, Maximum Heat Sealing tube diameter:6 mm



No Preheating Required, Ready to use startup



Splash Protection plate, Metal Shielding Casing for safety.



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada  
Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)