



TUBE SEALER BFH1H1

TUBE SEALER BFH1H1

VERTICAL INTELLIGENT TUBE SEALER



Triple Heat Dissipation, Continuous heat Sealing Capability
Wide Sealing Surface, Maximum Heat Sealing tube diameter:6 mm
No Preheating Required, Ready to use startup
Splash Protection plate, Metal Shielding Casing for safety.
Can be used in Parallel with Multiple Units, Ultra-Slim Body Design

SPECIFICATIONS

Model	BFH1H1
Heat Sealing Time:	0.5-2s
Indicator Light Colors:	Red/Blue
Grounding Protection:	Class I
Power Consumption:	250W during operation,10W in stand by
Weight:	4.5 kg
Operating Temperature:	0-40°C
Heat sealing TubeOuter Diameter:	2-6mm
RF frequency	40.68MHz
Spacing Adjustment	65,70,75,80,85,90,95,100mm
Power supply:	100V~120V/220V-240V AC
Dimensions:	336x65x173mm
Storage Temperature:	-20~7°C
Alt Name	Vertical Intelligent Tube Sealer

FEATURES

Triple Heat Dissipation, Continuous heat Sealing Capability



Wide Sealing Surface, Maximum Heat Sealing tube diameter:6 mm



No Preheating Required, Ready to use startup



Splash Protection plate, Metal Shielding Casing for safety.



Can be used in Parallel with Multiple Units, Ultra-Slim Body Design



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: info@biolabscientific.com | Website: www.biolabscientific.com