



## RECIPROCAL SHAKER BFL-802

# RECIPROCAL SHAKER BFL-802

3D SHAKER



Provide a gentle three-dimensional motion shaker at a fixed tilt angle  
Anti-slip silicone disc surface, better anti-slip effect, and better sample processing effect  
Adjustable rotational mixing speed  
Independent LCD/LED display of time and speed  
Incubator compatible

## SPECIFICATIONS

Model	BFL-802
Tilt angle	10°
Max. load capacity (with platform)	2kg
Motor type	DC motor
Motor input power	16W
Motor output power	10W
Speed range	10-80rpm
Speed display	LED
Timer display	LED
Time settings range	1min-99h59min
Voltage, Frequency	100-240V, 50/60Hz
Power	20W
Weight	3.7kg
Permissible ambient temperature and humidity	5-40°C, 80%RH
Dimension[WxDxH]	294 x 348 x 170mm
Protection class	IP21
Alt Name	Intelligent 3D Shaker

## APPLICATIONS

3D shaker used for uniform shaking/mixing in flasks, culture flasks, petri dishes and tubes. Ideal for culturing a variety of cell cultures, DNA extractions, distributing of cells and gel staining & destaining of cells.



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)