



TUBE ROLLER / ROTATOR BFL101 (BTUR-102)

TUBE ROLLER / ROTATOR BFL101

LCD DIGITAL TUBE ROLLER



LCD Display

Timer

LCD displays the speed and time

Rocking & rolling at variable speed

Adjustable speed range from 10 to 70 rpm

Six roller design for gentle and efficient rolling, and easy to clean

DC brushless motor quiet and maintenance free

Cold room and incubator compatible

SPECIFICATIONS

Model	BFL101
Old Model	BTUR-102
Amplitude	24mm
Motor type	Brushless DC motor
Rocking motion	Rocking and rolling
Max. load capacity	4kg
Number of rollers	6
Roller size [length]	280mm
Speed range	10-70rpm
Speed display	LCD
Timer	Yes
Timer display	LCD
Time setting range	1-1199min
Operation mode	Continuous/timer
Voltage, Frequency	100-240V, 50/60Hz
Power	30W
Dimension [DxWxH]	485 x 250 x 100mm
Weight	5.1kg
Permissible ambient temperature and humidity	5-40°C, 80%RH
Protection class	IP21
Alt Name	LCD Digital Tube Roller

FEATURES



LCD Display



Timer

LCD displays the speed and time

Rocking & rolling at variable speed

Adjustable speed range from 10 to 70 rpm

Six roller design for gentle and efficient rolling, and easy to clean

DC brushless motor quiet and maintenance free

Cold room and incubator compatible



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: info@biolabscientific.com | Website: www.biolabscientific.com