



## DUCTED FUME HOOD BFSD-303

# DUCTED FUME HOOD BFSD-303

## DUCTED FUME HOOD



1. Adjustable air speed: 9 levels.
  2. Microprocessor control system, LED display.
  3. Resistant to moderate acid and alkali.
  4. With memory function in case of power-failure.
  5. Manual front glass window, height adjustable.
  6. Built-in PP centrifugal blower; low noise, easy installation.
- LED Display, Digital LED display: Airflow Level  
Waterproof Socket  
Universal Wheel  
Water Remote Control  
Water Tap  
Water Tap & Water Sink

## SPECIFICATIONS

| Model                 | BFSD-303                                                                                                         |
|-----------------------|------------------------------------------------------------------------------------------------------------------|
| External Size(W*D*H)  | 1500*800*2515mm                                                                                                  |
| Internal Size(W*D*H)  | 1290*600*870mm                                                                                                   |
| Work Surface Height   | 900mm                                                                                                            |
| Max Opening           | 750mm                                                                                                            |
| Air Velocity          | 0.3~0.8m/s                                                                                                       |
| System Exhaust Volume | 930m <sup>3</sup> /h                                                                                             |
| Noise                 | ≤68dB                                                                                                            |
| Exhaust Duct          | PVC, Standard length; 4.3 meters, Φ300mm                                                                         |
| Pipe Strap            | 2 pcs                                                                                                            |
| LED Lamp              | 40W *1                                                                                                           |
| Blower                | Built-in PP centrifugal blower                                                                                   |
| Front Window          | Manual, 5mm toughened glass, height adjustable                                                                   |
| Power Supply          | 220V±10%, 60/50Hz; 110V±10%, 60Hz                                                                                |
| Consumption           | 500W                                                                                                             |
| Material Exterior     | 1.0mm cold-rolled steel with bacteria power coating.                                                             |
| Material Interior     | Compact laminate board with good acid and alkali resistance function                                             |
| Material Work table   | Chemical resistant phenolic resin                                                                                |
| Standard Accessory    | PP Water sink, Total load of 2 waterproof sockets: 500w, Base cabinet, Water tap, 4 meters Exhaust duct(9300mm). |
| Optional Accessory    | Air supply flow control valve, gas faucet.                                                                       |
| Gross Weight          | 335kg                                                                                                            |
| Package Main Body     | 1640*940*1900mm                                                                                                  |
| Package Base Cabinet  | 1640*940*1050mm                                                                                                  |
| Alt Name              | Ducted Fume Hood                                                                                                 |

## FEATURES

1. Adjustable air speed: 9 levels.
2. Microprocessor control system, LED display.
3. Resistant to moderate acid and alkali.
4. With memory function in case of power-failure.

- 5. Manual front glass window, height adjustable.
- 6. Built-in PP centrifugal blower; low noise, easy installation.

LED Display, Digital LED display: Airflow Level



Waterproof Socket



Universal Wheel



Water Remote Control



Water Tap



Water Tap & Water Sink





**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada  
Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)