



## DUCTED FUME HOOD BFSD-401

# DUCTED FUME HOOD BFSD-401

DUCTED PP FUME HOOD



1. It is safer to use anti-corrosive water tap.
2. Microprocessor control system, LED display.
3. With memory function in case of power-failure.
4. Made of porcelain white PP, resistant to acid, alkali and anti-corrosion.
5. Front window which is made of 5mm thick transparent toughened glass maximize light and visibility inside the fume hood, providing a bright and open working environment.

LED Display  
 Waterproof Socket  
 Water&Gas Remote Control  
 PP Sink, resistant to acid, alkali and anti-corrosion

## SPECIFICATIONS

Model	BFSD-401
External Size (W*D*H)	1047*800*2450mm
Internal Size (W*D*H)	787*560*700mm
Work Surface Height	820mm
Max Opening	740mm
Air Velocity	0.3~0.8m/s
Noise	≤68dB
Exhaust Duct	4.3 meters, φ250mm
LED Lamp	12w*2
Blower	Built-in PP centrifugal blower (2 blowers for FH1800(P) only); Speed adjustable
Front Window	Resistant to acid and alkali, Manual, 55mm toughened glass, height adjustable
Power Supply	AC220V±10%, 50/60Hz; 110V±10%, 60Hz
Consumption	400W
Material Main Body	Made of Porcelain white PP, thickness 8mm, resistant to strong acid, alkali and anti-corrosion
Material Work Table	Chemical resistant phenolic resin
Standard Accessory	LED light; Work table: Chemical resistant phenolic resin; 4.3 meters PVC duct ( 2 Pcs of 4.3 meters PVC duct for FH1800(P) only ), Diameter: 250mm; Pipe strap*2(4 Pcs for FH1800(P) only); RVV power cord (3*1.0mm <sup>2</sup> *3000mm); Base cabinet; Waterproof socket*2; Tail insert; Water tap(PP); Gas tap(PP); Water Sink; PP centrifugal blower*1(2 for FH1800(P)
Gross weight Main Body	137kg
Gross weight Base Cabinet	89kg or 80kg(Spllicable)
Package Size (W*D*H) Main Body	1188*938*1612mm
Package Size (W*D*H) Base Cabinet	1188*888*1000mm or 1200*1000*450mm(Spllicable)
Alt Name	Ducted PP Fume Hood

## FEATURES

1. It is safer to use anti-corrosive water tap.
2. Microprocessor control system, LED display.
3. With memory function in case of power-failure.
4. Made of porcelain white PP, resistant to acid, alkali and anti-corrosion.
5. Front window which is made of 5mm thick transparent toughened glass maximize light and visibility inside the fume hood, providing a bright and open working environment.

LED Display



Waterproof Socket



Water&Gas Remote Control



PP Sink, resistant to acid, alkali and anti-corrosion



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada  
Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)