



WALK IN FUME HOOD BFSD-803

WALK IN FUME HOOD BFSD-803

WALK-IN FUME HOOD



1. With memory function in case of power-failure.
 2. Operators are available to walk into the fume hood to operate if need.
 3. Large room exhaust system, suitable for large laboratory instruments and equipment.
- Water Sink
Water & Gas Remote, Control Valve
Water & Gas Tap
Application
Application

SPECIFICATIONS

Model	BFSD-803
External Size (W*D*H)	1800*800*2250mm
Internal Size (W*D*H)	1580*550*1670mm
Max Opening	1300mm
Exhaust Airflow Volume	1800m³h
Inflow Air Velocity	0.3~0.8m/s.
Noise	≤62dB
Vibration	Amplitude≤5µm
Illumination	≥800Lux
LED Lamp	16W*2
Power Supply	AC220V±10%, 50/60Hz; 110V±10%, 60Hz
Consumption	800W
Front Window	Manual, 55mm toughened glass,height adjustable
Material Exterior	1.0mm cold-rolled steel with bacteria powder coating.
Material Interior	Compact laminate board with good acid and alkali resistance function
Standard Accessory	External blower , LED lamp, Water tap, Gas tap, PP cup sink, Remote control water valve, Remote control gas valve, Waterproof sockets*4, 4.3 meters Φ300mm PVC exhaust duct
Sockets	Total load of 4 waterproof sockets: ≤500W
Package Size (W*D*H) Main Body	2010*1050*2450mm
Package Size (W*D*H) Exhaust Blower	1040*890*710mm
Gross Wight	390KG
Alt Name	Walk-in Fume Hood

FEATURES

1. With memory function in case of power-failure.
2. Operators are available to walk into the fume hood to operate if need.
3. Large room exhaust system, suitable for large laboratory instruments and equipment.

Water Sink



Water & Gas Remote, Control Valve



Water & Gas Tap



Application



Application



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada
Email: info@biolabscientific.com | Website: www.biolabscientific.com