



## RECIPROCAL SHAKER BGI-2507

# RECIPROCAL SHAKER BGI-2507

ORBITAL SHAKER



- Microprocessor PID controller, with timing function.
- Stainless-steel or alnico plate, non-eroding and easy clean.
- DC Brushless motor with long using life, wide speed control with long using life, wide speed control.
- The alarm will get off when the real shaking speed is 10% different with setting value, and motor will stop automatically.
- Speed controller ensures smooth start /stop which can prevent the liquid spill to damage the equipment.

## SPECIFICATIONS

Model	BGI-2507
Electrical Requirement	220V 50Hz
Type of Movement	Reciprocating
Shaking Speed Range	40~250 rpm
Amplitude	20mm
Temperature Range	-
Display Resolution	-
Power Consumption	60W
Platform Size (mm)	350x350
Default Platform	Spring wire racks
Packing Dimension	-
CBM	-
Net Weight	-
Gross weight	-
Heating plate function	-
Alt Name	Reciprocal Shaker



## APPLICATIONS

Microprocessor controller (with timing function)

Widely applicable for researches on bacteria cultivation, fermentation, hybridization, chemical and biochemical reaction.



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)