



## OVERHEAD STIRRER BGI-5203

# OVERHEAD STIRRER BGI-5203

## OVERHEAD STIRRER

The BD Series Overhead stirrer adopts a CNC stepless speed regulator, which is high-speed and convenient, and can digitally display the operating speed, making the machine safer and more reliable. It has advanced technology, low-noise mechanical reduction structure, small size, and large output torque. It is suitable for scientific research, colleges and universities, chemical industry, pharmaceuticals, medical units and other purposes.



4 blades propeller  
Length:400mm  
Diameter:50mm  
Material:316 stainless steel  
Application:Standard one,for mid-high speed  
4 blades propeller  
Length:350mm  
Diameter:65mm  
Material:PTEE  
Application:Standard one,for mid-high speed  
Flat hole propeller  
Length:400mm

## SPECIFICATIONS

Model	BGI-5203
Capacity	60L
Speed range	30~2200rpm
Speed display	LCD
Resolution	±1rpm
Torque	60N.cm
Max viscosity	80000mPas
Diameter	0.5~10mm
Exterior Dimension	160x80x180
Net weight	3.0kg
Protect class	IP42
RS232	
Voltage	AC220V50HZ/110V60HZ
Power	160W
Alt Name	Overhead stirrer

## FEATURES



4 blades propeller  
Length:400mm  
Diameter:50mm  
Material:316 stainless steel  
Application:Standard one,for mid-high speed



4 blades propeller  
Length:350mm  
Diameter:65mm  
Material:PTEE  
Application:Standard one,for mid-high speed



Flat hole propeller  
Length:400mm  
Diameter:68mm  
Material:316 stainless steel  
Application:gente mixing, mid-low speed



Flat hole propeller  
Length:350mm  
Diameter:68mm  
Material:PTEE Coating  
Application:gente mixing, mid-low speed



One line propeller  
Length:400mm  
Diameter:60mm  
Material:316 stainless steel  
Application:Low viscosity mixing mid-high speed



One line propeller  
Length:350mm  
Diameter:70mm  
Material:PTEE  
Application:Low viscosity mixing mid-high speed



Centrifugal impeller

Length:400mm

Diameter:90mm

Material:316 stainless steel

Application:The blades are flexible,good for small mouth round flasks mid-high speed



Centrifugal impeller

Length:350mm

Diameter:85mm

Material:PTEE Coating

Application:The blades are flexible,good for small mouth round flasks mid-high speed



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)