



VACUUM OVEN BGI1H9 (BOVA-7215)

VACUUM OVEN BGI1H9

VACUUM OVEN



- 304 stainless steel, mirror polishing processing, easy to clean and maintain.
 - PID controller with over temperature alarm and timing function ensures precise and reliable control, also save more than 40% heating time.
 - A big dual layer tempered glass on the door provides good observation.
 - Door adjustment system with silicon door gasket ensures better vacuity.
- Option
- KF25 Vacuum Port.
 - LED lights on the door.
 - Inert gas valve.

SPECIFICATIONS

Model	BGI1H9
Old Model	BOVA-7215
Electrical Requirement	AC220V 50HZ
Controller	LED display
Power Consumption	1500W
Temperature Range	RT-10~200°C
Display Resolution	0.1
Temperature Stability	±1°C
Vacuum Degree	133Pa
Chamber Volume	125L
Ambient Temperature	+5~40°C
Interior Dimension (WxDxH)mm	500x500x500
Exterior Dimension (WxDxH)mm	790x660x641
Shelves	3(pcs)-Independent temp. control
Chamber Material	304 Stainless steel
Alt Name	Vacuum Oven

APPLICATIONS

LED Microprocessor Controller (with timing function)

Vacuum oven is designed especially for drying material which is thermosensitive , oxidative, decomposable easily. It can also work with inert gas to dry some compound material.



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: info@biolabscientific.com | Website: www.biolabscientific.com