



## MUFFLE BOX FURNACE BGI1M6

# MUFFLE BOX FURNACE BGI1M6

## PROGRAMMABLE MUFFLE FURNACE



- Unique design of furnace door makes opening door safe and easy, ensure the heat of furnace will not leak out.
- Microcomputer PID controller, easy to operate, accurate, reliable and safe temperature control
- Corrosion-resistant light weight furnace ensure long-term life. (Firebrick furnace or ceramic fiber furnace can be optional)
- The excellent door seal makes the heat loss minimum and increases the uniformity of the temperature in the furnace.
- Programmable controller with 7 groups 63 steps, 0~5999min for each steps., each groups can set rising or remain temperature, and provide a program of temperature, time, heating power cycle.
- Programmable temperature controller can make experiments procedure more simple

## SPECIFICATIONS

Model	BGI1M6
Max. Temp	1200
Volume	7L
Furnace Dimension (WxDxH) mm	200x300x120
Exterior Dimension (WxDxH) mm	520x650x660
Electrical	380V/50HZ
Power	5KW
Heating Element	Nickel chrome wire
Alt Name	Programmable Muffle Furnace

## FEATURES

- Unique design of furnace door makes opening door safe and easy, ensure the heat of furnace will not leak out.
- Microcomputer PID controller, easy to operate, accurate, reliable and safe temperature control
- Corrosion-resistant light weight furnace ensure long-term life. (Firebrick furnace or ceramic fiber furnace can be optional)
- The excellent door seal makes the heat loss minimum and increases the uniformity of the temperature in the furnace.
- Programmable controller with 7 groups 63 steps, 0~5999min for each steps., each groups can set rising or remain temperature, and provide a program of temperature, time, heating power cycle.
- Programmable temperature controller can make experiments procedure more simple to realize automatic control. Door and furnace and body are all made of stainless steel which with anti-corrosion.

Safety function:

- The safety switch will automatic shutdown when door open ensures the safety of the operator.
- Over-flow, over-voltage, overheating and various safety measures to ensure safety.
- Ceramic fiberboard insulation material with good heat insulation effect, low temperature on shell surface.

Furnace:

- Ceramic fiber furnace (T series) with light weight, fast heating speed, saving energy and time etc. to satisfy the requirements under various conditions.
- Firebrick furnace (N series) use of traditional refractory materials, wide range of applications, long life and economic.



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada  
Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)