



## HOTPLATE BHMS-113

# HOTPLATE BHMS-113

LED HOTPLATE



LED screen display actual and accurate temperature  
Maximum temperature up to 550°C  
Separate safety circuits with safety temperature of 580°C  
External temperature control is possible by connecting temperature sensor (PT1000) with an accuracy of  $\pm 0.2^\circ\text{C}$   
Work plate provides excellent chemical-resistant performance and most efficient heat transfer  
"HOT" warning flashes when the workplate temperature is above 50°C

## SPECIFICATIONS

Model	BHMS-113
Work plate Dimension [W x D]	184x184mm (7 inch)
Work plate material	Glass ceramic
Heating position	1
Heating temperature range	Room Temp.-550°C, increment 5°C
Control accuracy of work plate	$\pm 10^\circ\text{C}$
Safety temperature	580°C
Temperature display	LED
Temperature display accuracy	$\pm 1^\circ\text{C}$
External temperature sensor	PT1000 (accuracy $\pm 0.2^\circ\text{C}$ )
Heating warning	50°C
Protection class	IP21
Power	1010W
Heating Power	1000W
Voltage, Frequency	100-120/200-240V, 50/60Hz
Dimension [WxDxH]	215x360x112mm
Weight	4.5kg
Permissible ambient temperature and humidity	5-40°C, 80%RH
Alt Name	LED Hotplate





**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada  
Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)