



## FFU (FAN FILTER UNIT) BJU-3603

## FFU (FAN FILTER UNIT) BJU-3603

### FFU (FAN FILTER UNIT)

FFU means Fan Filter Unit. It's equipped with Pre-filter and HEPA filter. The blower sucks air from the top of the FFU and filters it through the pre-filter and HEPA filter. Then filtered clean air is uniformly exhausted across the entire air outlet surface. It is suitable for obtaining a high-level clean environment in various settings.



## SPECIFICATIONS

|                               |                                                              |
|-------------------------------|--------------------------------------------------------------|
| Model                         | BJU-3603                                                     |
| External Size (WxDxH) (mm)    | 1175x1175x250                                                |
| Air Velocity                  |                                                              |
| Air Volume (m³/h)             | 1800~2200                                                    |
| Filter and Efficiency         | 1pcs Pre-filter                                              |
| HEPA Filter Size (WxDxH) (mm) | 1170x1170x70                                                 |
| Cleanliness Grade             | Class 100 (ISO14644.1 Class 5)                               |
| Sound Emission                | ≤65dB                                                        |
| Shell Material                | Aluminium coated zinc plate, anti-corrosion and light weight |
| Consumption                   | 245W                                                         |
| Power Supply                  | AC220V±10%, 50/60HZ; 110V±10%, 60Hz                          |
| Standard Accessory            | Pre-filterx1, HEPA filterx1, Blower.                         |
| Net Weight (kg)               | 35                                                           |
| Gross Weight (kg)             | 55                                                           |
| Shipping Size (WxDxH) (mm)    | 1335x1335x540                                                |
| Shipping Volume (m³)          | 0.96                                                         |
| Alt Name                      | FFU (Fan Filter Unit)                                        |

## APPLICATIONS

FFU is widely used in clean rooms, laminar flow cabinet, clean production lines, modular clean rooms and local Class 100 clean rooms and other application scenarios.



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)