



MOBILE CLEAN SAMPLING BOOTH BKF-1301

MOBILE CLEAN SAMPLING BOOTH BKF-1301

JC SERIES CLEAN SAMPLING VEHICLE



The glass can be moved up and down which is convenient and flexible for use. Adopting an adjustable air volume fan system with electrical remote control. Uninterruptible power supply for easy sampling and use. Using dust-free and fireproof high-density board materials as the framework.

SPECIFICATIONS

Model	BKF-1301
Internal Dimensions (W*D*H)	1730*635*930 (1300)
External Dimensions (W*D*H)	885*690*1910
Cleanliness	Level 100 @ $\geq 0.5 \mu\text{M}$ (Federal 209E)
Number of colony	≤ 0.5 pieces/dish · hour (Φ 90mm culture plate)
Average wind speed	0.25~0.45m/s
Noise	$\leq 62\text{dB}$ (A)
Vibration half peak	$\leq 5\mu\text{M}$ (X,Y,Z)
Illuminance	$\geq 300\text{LX}$
Power supply	AC single phase 220V/50Hz
Maximum Power consumption	600W
Weight	< 3
HEPA filter specifications and quantity	725x600x50
LED/UV lamp specifications and quantity	20Wx/20W
Alt Name	Series Clean Sampling vehicle

APPLICATIONS

The air passes through the primary filter, it is compressed into the static pressure box by a centrifugal fan, and then filtered by the HEPA filter before being blown out from the air outlet surface, forming a clean airflow. The clean airflow flows through the area that needs to be purified at a uniform cross-sectional wind speed, taking away the dust particles in the area, thus forming a high cleanliness working environment.



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: info@biolabscientific.com | Website: www.biolabscientific.com