



AIR SHOWER BKF-1505

AIR SHOWER BKF-1505

AIR SHOWER

The air in the air shower room enters the static pressure chamber through the primary filter under the action of the fan, and is efficiently discharged to maintain a safe and reliable experimental environment. After the air filter is filtered, clean air is sprayed out at high speed from the spray nozzle in the air shower room, with the nozzle angle Adjustable, effectively blowing away dust adhering to the surface of personal characteristics or carried items, and recycling the blown dust into the primary air Filter, this circulation can achieve the purpose of wind drenching.



The material of the air shower is made of color steel plate, which is integrally formed, with high cost-effectiveness and elegant appearance.
Fully utilize design principles to design a smaller exterior size for the air shower room, providing limited access
Selection provides greater flexibility.
The wind drenching time is adjustable from 0 to 99 seconds.
Infrared automatic sensing of wind port opening.
The LCD control panel achieves human-machine interaction, voice broadcasting, and timing functions.
Stainless steel air shower nozzle.
The small air shower room is an integral unit, which is more convenient to install and use; The large wind shower room is a split type. Convenient transportation

SPECIFICATIONS

Model	BKF-1505
Internal Size (W*D*H)	700*2400*1900
External Size (W*D*H)	1300*2400*2050
Filter efficiency	≥99.7% @ ≥0.5μm
Time	0~99s (adjustable)
The nozzle number	36
Jet diameter	Φ30mm
Nozzle mouth material	Stainless steel
Ejection wind speed	15~20m/s
Power supply	AC, single phase 220V/50Hz
Max. Power	2000W
Suited for person	Four person/double sides air blow
Alt Name	Air shower

FEATURES

The material of the air shower is made of color steel plate, which is integrally formed, with high cost-effectiveness and elegant appearance.

Fully utilize design principles to design a smaller exterior size for the air shower room, providing limited access

Selection provides greater flexibility.

The wind drenching time is adjustable from 0 to 99 seconds.

Infrared automatic sensing of wind port opening.

The LCD control panel achieves human-machine interaction, voice broadcasting, and timing functions.

Stainless steel air shower nozzle.

The small air shower room is an integral unit, which is more convenient to install and use; The large wind shower room is a split type. Convenient transportation and push.

It can be equipped with automatic interlocking, and the material can be customized.

APPLICATIONS

Air shower series products are a kind of general partial purification equipment, installed between clean room and non clean room. When people and goods to enter the clean area subject to the wind rain shower, blow out the clean air can remove people and goods carried by dust, can effectively block or reduce dust source in clean areas. Air shower before and after the two doors for electronic lock, but also have the effect of air brake, prevent raw air into the clean area.



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: info@biolabscientific.com | Website: www.biolabscientific.com