



## MULTISTATION STIRRER BMSS-105

# MULTISTATION STIRRER BMSS-105

## MULTISTATION STIRRER



Maintenance-free brushless DC motor  
Maximum speed 1100 rpm  
Maximum temperature of work plate up to 120°C  
Stainless steel work plate, covered with silicone cushion, provides excellent heating uniformity and skid resistance

## SPECIFICATIONS

Model	BMSS-105
Work plate dimension[W x D]	180x450mm
Work Plate material	Stainless steel covered with silicone cushion
Motor type	Brushless DC motor
Stirring positions	10
Max. stirring quantity	0.4Lx10
Max. magnetic bar [length]	40mm
Speed range	0-1100rpm
Speed display	scale
Temperature display	scale
Heating temperature range	Room temp.-120°C
Over temperature protection	140°C
IP Protection class	IP20
Motor rating output	4W
Power	490W
Heating Power	470W
Voltage, Frequency	100-120/200-240V, 50/60Hz
Dimensions[WxDxH]	182x622x65mm
Weight	3.2kg
Permissible ambient temperature and humidity	5-40°C, 80%RH
Alt Name	Multistation Stirrer



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)