



MICROWAVE DIGESTER BMWD-102

MICROWAVE DIGESTER BMWD-102

MICROWAVE DIGESTION SYSTEM



- Compatible with 6/8/10/12-position sample rotor.
- Imported contactless IR sensor and pressure sensor, real-time display the temperature and pressure of sample solution (NOT Vessel Wall) in each vessel and show T&P scanning curve.
- No consumables, e.g. bursting disk, sealing cup, etc. lower maintenance cost.
- Equipped with a smart 7 inches touch screen, user-friendly UI.
- Pre-installed multiple international application methods. Users can also edit, modify and delete the methods.
- Equip with 316L stainless explosion-proof cavity, coated with multi-layer anti-corrosive and heat resisting coatings, which greatly prolongs its service life and ensures the safety of operation.
- High power turbulent air cooling design makes fast cooling.

SPECIFICATIONS

Model	BMWD-102
Vessel Quantity	8
Temperature Monitoring	Contactless IR Sensor Temperature MonitoringEach Vessel Temperature ControlledTemperature Controlling Range: 50-400°CMax. Working Temperature: 250°CTemperature Accuracy: $\pm 0.1^{\circ}\text{C}$
Pressure Monitoring	Contactless Sensor Pressure monitoringEach Vessel Pressure ControlledPressure Controlling Range: 0-15MPaMax. Working Pressure: 6MPaPressure Accuracy: $\pm 0.01\text{MPa}$
Vessel Volume	100mL
Sample Vessel Material	Imported TFM
Protection Vessel Material	PEEK+Glass Fiber
Display	7 inches Color Touch Screen
Rotation	One Direction 360° continuous rotating
Microwave Cavity	316L stainless steel cavity with corrosion-proof coating
Microwave Power	0-1000W (Adjustable)
Microwave Leakage	$< 5\text{mW}/\text{cm}^2$
Air Exhaust	High power corrosion-proof air blower
Power	AC 220V $\pm 10\%$, 10A, 50/60Hz
Alt Name	Microwave Digestion System

FEATURES

- Compatible with 6/8/10/12-position sample rotor.
- Imported contactless IR sensor and pressure sensor, real-time display the temperature and pressure of sample solution (NOT Vessel Wall) in each vessel and show T&P scanning curve.
- No consumables, e.g. bursting disk, sealing cup, etc. lower maintenance cost.
- Equipped with a smart 7 inches touch screen, user-friendly UI.
- Pre-installed multiple international application methods. Users can also edit, modify and delete the methods.
- Equip with 316L stainless explosion-proof cavity, coated with multi-layer anti-corrosive and heat resisting coatings, which greatly prolongs its service life and ensures the safety of operation.
- High power turbulent air cooling design makes fast cooling.
- Professional electromagnetic protection design, compatible with high-level microwave leakage protection standards.



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada
Email: info@biolabscientific.com | Website: www.biolabscientific.com