



## FLOOR STANDING SHAKING INCUBATOR BSBT-2204

# FLOOR STANDING SHAKING INCUBATOR BSBT-2204

## SHAKING INCUBATOR



### LCD Microprocessor Controller (with timing function)

- Intelligent LCD screen control, parameters real time display, operation easily.
- Temp, rotation speed and time etc parameters fast setting.
- User's set parameters can be stored automatically when power off suddenly, and it resume last program settings when power on.
- Combine incubator, shaker functions together with small space, huge capacity
- Silent running
- Big transparent big view windows, platform and chamber are made of stainless steel, anticorrosion and easy to clean.
- Brushless DC motor, large start torque, wide speed adjustment, free maintenance.

## SPECIFICATIONS

|                              |                             |
|------------------------------|-----------------------------|
| Model                        | BSBT-2204                   |
| Electrical Requirement       | 220V 50Hz                   |
| Shaking Speed Range          | 40~300r/min                 |
| Amplitude                    | 26mm                        |
| Temperature Range            | 4~65°C                      |
| Display Resolution           | 0.1°C                       |
| Temperature Uniformity       | ±1°C (Test point is 37°C)   |
| Temperature Fluctuation      | ±0.2°C (Test point is 37°C) |
| Power Consumption            | 1300W                       |
| Platform Size (mm)           | 920x500                     |
| Standard Configuration       | 250mlx45                    |
| External Dimension (WxDxH)mm | 1250x660x915                |
| Timing Range                 | 0~5999min                   |
| Packing Dimension            | 139*83*112                  |
| CBM                          | 1.29                        |
| Net Weight                   | 210.00                      |
| Gross weight                 | 289                         |
| Alt Name                     | Shaking Incubator           |

## FEATURES

### LCD Microprocessor Controller (with timing function)

- Intelligent LCD screen control, parameters real time display, operation easily.
- Temp, rotation speed and time etc parameters fast setting.
- User's set parameters can be stored automatically when power off suddenly, and it resume last program settings when power on.
- Combine incubator, shaker functions together with small space, huge capacity
- Silent running
- Big transparent big view windows, platform and chamber are made of stainless steel, anticorrosion and easy to clean.
- Brushless DC motor, large start torque, wide speed adjustment, free maintenance.
- Three-eccentric axis balance drive ensures all samples in the shaker platform movements at the same rotation frequency. Durable structure guarantees the shaker incubator can work properly no matter full load or high speed working.
- The ultraviolet lamp can sterilize the chamber regularly.
- Fluorine free design, environmental non-free refrigerants.

#### Safety

- Safety door switch, auto pause operation when door is opened.
- Smooth start and stop system prevents liquid spillage.
- Auto-controller of fan speed to prevent damage to the samples.
- Self-diagnosis function, it will display error when failure.
- Temperature-limiting alarm system, auto switch off when over-temperature.

#### Option

- RS485 connector or USB interface can connect computer record and inspect the parameters and the variations of temperature.
- Intelligent programmable temperature controller.
- Embedded Printer.



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)