



# FLOOR STANDING SHAKING INCUBATOR BSFT-1902

# FLOOR STANDING SHAKING INCUBATOR BSFT-1902

## CHEST TYPE SHAKER INCUBATOR



Colorful intelligent touch screen control:

1. Adopt 4.3 inches touch screen , intelligent touch screen control, parameters real time display, operation easily.
2. Temp, rotation speed and time etc parameters fast setting.

Humanization design:

Combine incubator, shaker functions together with small space, huge capacity. Colorful touch screen controller, menu operation interface, multi data display at one screen, easily to observe and operate.

Silent running.

Fluorine-free design, environmental friendly.

Big transparent big view windows, platform and chamber are made of stainless steel, anti-corrosion and easy to clean.

## SPECIFICATIONS

Model	BSFT-1902
Power supplies	AC220V 50HZ
Speed range	40 - 300 rpm
Amplitude	26mm
Control temp. range	RT+5 - 80°C
Temp. resolution	0.1°C
Timer range	1 - 99h59min
Rated power	1050W
Platform size (mm)	920x500
Overall size WxDxH (mm)	1200x730x930
Standard configuration	250mlx45
Packing Dimension	-
CBM	-
Net Weight	-
Gross weight	-
Alt Name	Chest Type Shaker Incubator

## FEATURES

Colorful intelligent touch screen control:

1. Adopt 4.3 inches touch screen , intelligent touch screen control, parameters real time display, operation easily.
2. Temp, rotation speed and time etc parameters fast setting.

Humanization design:

Combine incubator, shaker functions together with small space, huge capacity.

Colorful touch screen controller, menu operation interface, multi data display at one screen, easily to observe and operate.

Silent running.

Fluorine-free design, environmental friendly.

Big transparent big view windows, platform and chamber are made of stainless steel, anti-corrosion and easy to clean.

Quality guaranty:

- User's set parameters can be stored automatically when power off suddenly, and it resume last program settings when power on.
- PID microcomputer control temp. and shake frequency with timer.
- Compressor and cycle fan etc key components are reliable suppliers, environmental non-free refrigerants.

Uninterrupted performance guaranty:

- Brushless DC motor, large start torque, wide speed adjustment, free maintenance.

Three-eccentric axis balance drive:

- Three-eccentric axis balance drive ensures all samples in the shaker platform movements at the same rotation frequency.
- Durable structure guarantees the shaker incubator can work properly no matter full load or high speed working.

Convenient data process:

- Equip with USB as options, record temp. parameter changes (option).
- Equip with RS232 data interface, through software to remote control machine performance (option).
- Above two options can be selected only one.

Sterilization system:

- The ultraviolet lamp can sterilize the chamber regularly.

Safety:

- Protection on instruments: Comply international standard secondary temp. limiter alarm system, alert the operator with sound and light alarms, ensure operator is safe without any accident.
- Protection on key components: Key components have over current, over temp., over load etc safety protection, it can prevent instruments accidents without precautions.
- Protection on samples: Working chamber temperature higher or lower the set temp., alarm starter cut down the heater, alert the operator with sound and light alarms.
- Protection on operator: Cabinet and door is special designed for insulation, low heat of cabinet body, ensure operator use instrument without burnt.
- Breakdown message provided: When the instrument breakdown, the breakdown messages show on the screen to help operator easily check.

Multi-segment programmable control:


- Multi-segment temp., speed, time program at the same time.
- It has normal mode or programmable mode for running. Preset parameter and work data can be shown at the same time. It simplified complicated culture requirements and realize auto control and run.

Feature extension (option):

- CO<sub>2</sub> concentration monitor and control.
- Lighting control.
- Humidity control.



USB interface



PU foamed handle



25mm test hole



304 mirror stainless steel



Pneumatic gas spring holder



Pressure balance hole

## APPLICATIONS

Floor standing Shaker incubator combines incubator and shaker functions together, it uses new outlook design with big touch screen,. Adopt the latest technology of motor driven system, large torque, stable work, low noise and fast heat dissipation and long lifetime. It is widely used Cell culture, fermentation, biochemistry, enzyme research experiment or medium production experiment. Especially suitable for medium production, it solves the user's problem by advanced design and high precise manufacturing art craft.

## MORE INFO

Max. flask clamps can be placed (single layer)

Flask (pcs)	BSI21 / BSI21C	BSI31 / BSI31C
50 ml	82	116
100 ml	50	66
250 ml	28	45
500 ml	23	28
1000 ml	15	18
2000 ml	8	13



**Biolab Scientific Ltd.**

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada

Email: [info@biolabscientific.com](mailto:info@biolabscientific.com) | Website: [www.biolabscientific.com](http://www.biolabscientific.com)