



TUBE ROLLER / ROTATOR BTUR-102

TUBE ROLLER / ROTATOR BTUR-102

LCD DIGITAL TUBE ROLLER



LCD displays the speed and time
Rocking & rolling at variable speed
Adjustable speed range from 10 to 70 rpm
Six roller design for gentle and efficient rolling, and easy to clean
DC brushless motor quiet and maintenance free
Cold room and incubator compatible
LCD Display
Timer

SPECIFICATIONS

Model	BTUR-102
Amplitude	24mm
Motor type	Brushless DC motor
Rocking motion	Rocking and rolling
Max. load capacity	4kg
Number of rollers	6
Roller size [length]	280mm
Speed range	10-70rpm
Speed display	LCD
Timer	Yes
Timer display	LCD
Time setting range	1-1199min
Operation mode	Continuous/timer
Voltage, Frequency	100-240V, 50/60Hz
Power	30W
Dimension [DxWxH]	485 x 250 x 100mm
Weight	5.1kg
Permissible ambient temperature and humidity	5-40°C, 80%RH
Protection class	IP21
Alt Name	LCD Digital Tube Roller

FEATURES

LCD displays the speed and time
Rocking & rolling at variable speed
Adjustable speed range from 10 to 70 rpm
Six roller design for gentle and efficient rolling, and easy to clean
DC brushless motor quiet and maintenance free
Cold room and incubator compatible



LCD Display



Timer



Biolab Scientific Ltd.

Trillium Executive Center, East Tower, 675 Cochrane Dr, Markham, Ontario L3R 0B8, Canada
Email: info@biolabscientific.com | Website: www.biolabscientific.com